### Fameccanica Life+ Newsletter







Life+ Newsletter • Issue 5 • October 2014







Fameccanica presentation at Outlook™ 2014 Conference

#### Project Mid Term Conference at Outlook 2014, Barcelona



Fameccanica Life+ Glueless Project Mid Term Conference was held on Friday 26<sup>th</sup>,

2014 in Barcelona, Spain, as part of the wider OUTLOOK 2014 Conference organized by Edana, the European association serving the nonwovens and related industries.

With more than 420 delegates from across the nonwovens and related industries, OUTLOOK<sup>TM</sup> was again confirmed as one of the most important events for the personal care and hygiene products industries.

In opening the conference, Pierre

Wiertz, General Manager of EDANA reminded delegates that there was a close relationship between many of the conference themes, and EDANA's daily mission to support the growth and promote the sustainable development of the industry.

This was in fact one of the key reasons for Fameccanica to promote its project at this specific event. Fameccanica presented all the key achievements already reached at that stage, like completion of the step pertaining GLUELESS<sup>TM</sup> lamination of back ears for baby diapers, plus initial test results of GLUELESS<sup>TM</sup> application of ADL and ELASTICS.






#### Friday 26 September 2014

11.45 > 12.15

#### LIFE+ INITIATIVE FOR ENVIRONMENTAL IMPACT REDUCTION IN AHP PRODUCTION PROCESSES

- What is EU's LIFE programme
- The purpose of Fameccanica Life+ Glueless project and key R&D project steps
- The first achievement: Glueless lamination of back ears for baby diapers
- · Other activities already carried on for the target product features (case of baby diaper construction)
- A look at the diapers with the new construction: product performances test results

Alessandro D'Andrea, Marketing and Innovation Manager, Fameccanica Data S.p.A. (Italy)



## GLUELESS™ application of ADL: process initial test results – Peel Force Test

Peel force is considered mainly as a "process requirement", as it is required for runnability in the converting machine that the ADL is properly bonded to the topsheet. Test conducted at high speed showed that:

NW: All the Top sheet Nonwovens analyzed<sup>2</sup> have a good attitude to be welded even if they come from different suppliers.

ADL: the majority of commercial material tested has a good attitude to being welded, if containing at least small compatible termoplastic resin. According to the test results, the best way to weld using ultrasonic equipment and ADL with a NW topsheet is to use a bi-component ADL containing PolyPropylene to seal with a PP-based NW top sheet. The several ADLs tested from different suppliers contributed to the making of a benchmark.


<sup>2</sup> Commercially available Polypropylene-based spunbonded


# GLUELESS™ application of ADL: Product performances initial test results - Acquisition Time and Wetback

Samples of the final diaper element assembly with glueless ADL have been subject to product performance tests relevant to Acquisition Time and Wetback.

Both tests gave positive results as the comparative tests<sup>3</sup> of product performance vs. traditional technologies shows that the GLUELESS<sup>TM</sup> solution offers equivalent or even improved results than the traditional technologies.

<sup>3</sup> Test conducted with benchmark ADL#5 (PP/PE bico fiber)





Wetback (g)

0,25

0,15

0,1

0,05

0

ADL application with glue application ASSET#1 application ASSET#2

Slightly improved behaviour in wetback test